

| Model | B-25T | B-30T | B-30P |
|--------------------------|------------------------|------------------------|------------------------|
| Respiratory mode | CPAP, S/T, S, T | CPAP, S/T, S, T | CPAP, S/T, S, T, APCV |
| Parameters | | | |
| IPAP | 4-25cmH ₂ O | 4-30cmH ₂ O | 4-30cmH ₂ O |
| EPAP | 4-23cmH ₂ O | 4-25cmH ₂ O | 4-25cmH ₂ O |
| Isens | Auto, 1-6 level | Auto, 1-6 level | Auto, 1-6 level |
| Esens | Auto, 1-6 level | Auto, 1-6 level | Auto, 1-6 level |
| Islop | 1-6 level | 1-6 level | 1-6 level |
| InspTime | 0.5-4s | 0.5-4s | 0.5-4s |
| Max-InspTime | 0.5-4s | 0.5-4s | 0.5-4s |
| Min-InspTime | 0.5-4s | 0.5-4s | 0.5-4s |
| BPM | 3-40bpm | 3-40bpm | 3-40bpm |
| VAF settings | - | - | Available |
| Target VT | - | - | 50-2000ml |
| Ramp | 0-60min | 0-60min | 0-60min |
| Auto-On | On/Off | On/Off | On/Off |
| Auto-Off | On/Off | On/Off | On/Off |
| Auto-air compensation | Yes | Available | Available |
| Auto-adjustment altitude | Yes | Available | Available |
| Noise Level | ≤30dBA | ≤30dBA | ≤30dBA |
| Humidifier | 0-5 level | 0-5 level | 0-5 level |
| Configuration | | | |
| Screen | 3.5" colorful LCD | 3.5" colorful LCD | 3.5" colorful LCD |
| SpO2 Kit | Optional | Optional | Optional |
| Data storage | TF card | TF card | TF card |
| Dimension | 280*200*112mm | 280*200*112mm | 280*200*112mm |
| Weight | 2.2Kg | 2.2Kg | 2.2Kg |



ResPlus BPAP Series

For OSAHS & Respiratory insufficient patients



Scan to know more



BYOND 比扬医疗
Service call: 400-066-7111
Add: Beyond Zone, Lijiacun Rd, Xueshi Street,
Yuelu District, 410208 Changsha, China

BYOND 比扬
Pioneer in Life Science

3.5" colorful LCD screen

Provide vivid information in one page and more legibility;
User interface design to enable fast-setup.

Real-time data monitoring

Track the monitoring treatment data in real time.

Master core-technology

Imported Swiss pressure sensor cooperates with innovative algorithm to fulfill greater sensibility.

Dial Design

Rotate one key to complete various operations.

Lower dBA


Less noise achieved by high-quality Blower.

Separable design for host and humidifier


Flexible choices for therapy place are allowed by separable design.

Heating Humidifier

5 temperature levels for humidifier are available; Designed to prevent back flow and be detachable to clean easily.



Main interface



Data monitoring interface

Multiple respiratory modes

CPAP、S、T、SIT、APCV suitable for various respiratory insufficient patients.

Auto-sensibility

Isens and Esens are automatically adopted to individual's treatment.

VAF

Maintain a target tidal volume to meet patients' needs.

A variety of Alerts

Safer use is ensured by alerts, including power down, air leakage, high/low pressure, ect.

InspTime limitation

User can choose a period of time to inhale by setting the max- and min-InspTime, which ensures effective treatments.

